Scintica



HIGH PERFORMANCE AND RELIABILITY, TO DELIVER EVERYDAY

Since 1993 Baker Ruskinn have been working with Microbiologists all around the world, to fully support their needs, delivering high performing anaerobic and microaerophilic solutions.

We at Baker Ruskinn understand the growing demands being made on today's Microbiologists and their laboratories. We know how important it is to have high performing equipment that you and your hardworking teams can rely on. That's why we are dedicated to deliver products that serve the people who process thousands of important samples every day.



EFFICIENCY & RELIABILITY

Save time in getting patient samples efficiently into correct anaerobic conditions, with our fast interlock purge cycle times and Single Plate Entry System (SPESTM). Go further with our remote monitoring and control system, allows complete control wherever you are.

EASE OF USE

Access your workstation quickly & easily with our Ezee Sleeve™ direct-hand access port system. It's also so easy to clean with the removable pop-off front cover (Pop-Off™).

ACCURACY & CONTROL

Check your environmental conditions at a glance, with our clear digital on-screen colour-coded display, set to your specific parameters. With an optical sensor & HEPA filtration as standard, you can truly rely on the accuracy of set conditions.

CAPACITY & FLEXIBILITY

Process more plates in one controlled environment with our high capacity workstations (up to 500 plates). Our modular design gives ultimate flexibility to expand and upgrade your workstation to offer a dual chamber controlled environment.




*Only available on Concept 400-M

**Only valid if annual service schedule implemented

t and and Internal HEPA filtration as standard

Fast interlock

purge cycle time



The Concept range has been rigorously tested to maximize productivity of systemized anaerobic or microaerophilic incubation; bringing together a host of features that you can trust, bringing immediate benefits to your busy laboratory. The optional removable pop-off front cover (Pop-Off™) makes set-up and cleaning so easy; the modular-design provides users with true flexibility to expand and upgrade work spaces. It is by getting the small things right that sets this range apart. We know just how crucial it is for your equipment to support your teams to deliver effectively and efficiently every day.





Single Plate Entry System

or removal of plates

(SPES™) for instant insertion

Direct-hand access using

Ezee Sleeve™ port systems

REFINED TO SUIT YOUR SPECIFIC NEEDS





Scan the QR code to see more about the Concept range

There are four models in the Concept range, each one carefully refined to suit your specific needs, with advanced ergonomic design providing excellent hand access and rapid plate loading. Ideal for varying capacity workloads and providing the best primary isolation rates for your anaerobic and microaerophilic cultures.



Concept 400

Perfect for mid-range anaerobic workloads

210.3L working anaerobic volume

EXTERNAL DIMENSIONS

	mm	in		
Width	1252	49.3		
Height	1025	40.4		
Depth	797	31.4		



Concept 400-M

Perfect for mid-range anaerobic or microaerophilic workloads

210.3L working anaerobic volume

EXTERNAL DIMENSIONS

	mm	in
Width	1252	49.3
Height	1025	40.4
Depth	797	31.4



Concept 500


Perfect for mid-range workloads, with larger interlock

210.3L working anaerobic volume

EXTERNAL DIMENSIONS

	mm	in
Width	1392	54.8
Height	1025	40.4
Depth	797	31.4





Concept Dual Chamber 1000

For large anaerobic workloads and larger batch EXTERNAL DIMENSIONS sizes, or when two different atmospheres are needed. (Please ask about our dual chamber microaerophilic options)

Two independently controllable chambers, each 210.3L

EXTERNAL DIMENSIONS				
	mm	in		
Width	2404	94.6		
Height	1025	40.4		
Depth	797	31.4		



*Final product may differ from visuals

Scintica:

BAKER RUSKINN

VERSION NO.003

Get in touch today to hear how we can work with you

For U.K. / global inquiries: sales@bakerruskinn.com +44 (0) 1656 645988

For U.S. inquiries: bakerco@bakerco.com +1 (800) 992-2537

www.bakerco.com

Concept

ANAEROBIC & MICROAEROPHILIC WORKSTATIONS